



## RETURNABLE CYLINDER PROGRAM

For almost 40 years Calgaz has prided itself on producing and delivering calibration gas mixtures, equipment and service of unsurpassed quality and reliability. From the beginning, our innovative and talented team of engineers and lab technicians in Cambridge, Maryland, has focused on developing new products and processes that change the way you use calibration gas. Most of these have become industry-standard, including the 5/8" x 18 valve; the four-in-one gas mixture; the "push button" regulator; the 2AL, 34L aluminum cylinder; the revolutionary Demand Flow Regulator; and the "one way valve."

Over the last 20 years, Calgaz has been awarded eight U.S. patents and we have several more pending.

**We are now very excited to introduce Calgaz Plus, our latest offering that provides an efficient solution to our customers who are eager for returnable cylinders. The Calgaz Plus returnable cylinder program is good for you – and it's good for the environment.**

## THE CYLINDER SIZES AVAILABLE IN THE CALGAZ PLUS RETURNABLE LINE ARE:



*These cylinders have received DOT and TC approvals. The Calgaz Plus 625 and Calgaz Plus 850 cylinders are ISO 7866 UN-approved.*

The Calgaz Plus 60 and the Calgaz Plus 116 have the benefit of being nearly the same size as our existing Calgaz 34 and Calgaz 58 cylinders, but hold almost twice the volume. This means fewer cylinder changeovers for auto-calibration stations. It also reduces the cost of instrument calibration.

**The benefit to the environment of Calgaz Plus cylinders is obvious. It means fewer cylinders in landfills!**

All cylinders in the Calgaz Plus line are 100% aluminum and, once emptied, may be easily returned without charge to the Cambridge, Maryland, facility. The benefit to you is an easy, efficient way to manage empty cylinders.



## Calgaz Plus returnable cylinders are easy to return.

We designed the Calgaz Plus return program to be as simple and convenient as possible. Each Calgaz Plus cylinder is individually boxed. When you receive your cylinder, save the box to use to return the empty cylinder. The box flattens for easy storage. Return instructions and the return shipping label are already on the box! When you are ready to return your empty Calgaz Plus cylinder, just follow the three steps below.

## RETURN PROCESS:

**NOTE:** Remember to always use safety glasses when working with high pressure gases and regulators. Familiarize yourself with the Safety Data Sheet (SDS) before use.



**Step 1.** Ensure the Calgaz Plus cylinder is empty. While holding the gauge and regulator away from your face, attach regulator to the cylinder. In a well-ventilated area, release any residual contents until the gauge reads “zero” or “empty.” If the cylinder has a hand wheel, make sure the hand wheel is returned to the “closed” position when empty. Remove the regulator from the cylinder.



**Step 2.** Place the empty Calgaz Plus cylinder in the return box included in the original shipment and seal the package.



**Step 3.** Remove the instruction label on the return box to reveal the return shipping label underneath. Give the package to the listed shipper for return.

Please note – only U.S.-based customers may participate in the return program and only Calgaz Plus cylinders may be returned using this process. All others should follow local recycling or disposal regulations.

If you misplace your return box, visit [www.calgaz.com](http://www.calgaz.com) for alternate shipping instructions.

Our commitment to being a trusted partner that adds value is important to us. We prove this every day by delivering only the highest quality products and services, by understanding the industries we serve and by exceeding the expectations of our customers.

For more information about Calgaz Plus returnable cylinders or any other Calgaz product, please contact a customer service representative by phone (1-800-638-1197) or by email ([info@calgaz.com](mailto:info@calgaz.com)).